



1551 S. Vineyard Avenue  
Ontario, CA 91761  
(909) 923-1973

## **WIRING SCHEMATICS**

**FOR SOFTWARE VERSIONS 320.46 AND  
HIGHER**

**FOR CURTIS 1239 CONTROLLER**

**MARINE CONVERSION**

**FOR DUAL MOTOR**

**APPLICATION**

**REVISION: A**  
**Date 6/30/15**



**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

## DUAL MOTOR – 1239 CONTROLLER SECONDARY MOTOR SCHEMATICS

REVISIONS		
REV	DESCRIPTION	APPROVED
A	Initial Release	10/28/2014

### NOTES:


(\*1) Use supplied Contactor.

(\*2) Use supplied Pre-Charge Resistor and Relay (Tyco Electronics Part # T9AP1D52-12). For Coil connection, connect to small terminals.

(\*3) A Battery Management System (BMS) is strongly recommended if Lithium Ion batteries are used. Possible source of BMS is Ewert Energy System's ORION BMS ([www.orionbms.com](http://www.orionbms.com))

(\*4) Use Pack Fuse rated at 400A for Single controller applications. For Dual controller use 800A Pack fuse.


(\*5) Only for Dual motor application. Use Controller Fuse rated at 400A for each controller.



**NOTICE:** This drawing is the property of HI Performance Electric Vehicle Systems, Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	Initial Release	10/28/2014

## GAUGE CONNECTION SCHEMATIC



### NOTES:


(\*1) Tachometers that are designed to Work off of an ignition coil may not f in function in this application. Some Tachometers may need a pull up resistor of 4.7K  $\Omega$

CAD TYPE VISIO	APPLICABLE SOFTWARE      Version 320.46		
UNIT NONE	DRAWING      1010-BOAT-PRI		
DRW SIZE A	TITLE      1239 CONTROLLER MARINE GAUGES		
DATE 10/28/14			
SUPPLIER PART			
SCALE none	SHEET   1 OF 1	REVISION      A	HPEVS

**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	Initial Release	1/5/2015

# ENGAGE 7 CONNECTION SCHEMATIC




CAD TYPE VISIO	APPLICABLE SOFTWARE			
UNIT NONE	DRAWING 1010-ENGAGE7			
DRW SIZE A	TITLE			
DATE 1/5/15	ENGAGE 7 HARNESS			
SUPPLIER PART				
SCALE none	SHEET 1 OF 1		REVISION A	HPEVS


NOTICE: This drawing is the property of Hi Performance Electric Vehicle Systems, Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS, (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	Initial Release	10/28/2014

## TRANSDUCER CONNECTION SCHEMATIC



OR




### NOTES:

(\*1) Recommended Transducer:  
Honeywell, Part  
PX2EF1XX030PAAAX. Output:  
5V; Voltage Input: 4.75- 5.25 V;  
Operating Pressure: 30 PSI  
Possible Supplier: DIGIKEY  
P/N:480-5806-ND

CAD TYPE VISIO	APPLICABLE SOFTWARE      Version 320.46		
UNIT NONE	DRAWING      1010-BOAT-PRI		
DRW SIZE A	TITLE  1239 CONTROLLER MARINE TRANSDUCER		
DATE 10/28/14			
SUPPLIER PART			
SCALE none	SHEET   1 OF 1	REVISION      A	HPEVS

**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	INITIAL RELEASE	3/12/2013



CAD TYPE VISIO	CAD LOC.	CAD FILE	DRW SIZE A
OPER. NO.	UNIT	DRAWING 1010-ACUITY-INSTALL	
DESIGN	DETAIL	TITLE	
CHECKED	SAFETY	ACUITY INSTALLATION	
SCALE NONE	DATE 3/12/13	REVISION A SHEET 1 OF 1	HPEVS

## THROTTLE CONFIGURATION


Depending on the type of throttle used for the application, the different types of throttle configurations are listed within the table below. Electrical schematics are also included within the following pages.

THROTTLE CONFIGURATION	TYPE
ELECTRONIC without SWITCH	TYPE 2
2 WIRE with SWITCH 0-5k $\Omega$	TYPE 3
3 WIRE with SWITCH 0-5k $\Omega$	TYPE 2
CURTIS PB8 THROTTLE ASSEMBLY	TYPE 2
WIG WAG 3 WIRE	TYPE 4



**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	INITIAL RELEASE	2/3/2015



## TYPE 2 ELECTRONIC THROTTLE

## MARINE APPLICATION

\*Typical connection, verify correct voltage and connection in throttle documents or instructions.


Not all Electronic Throttles supported

\*\* When Electronic pedal is used, the GREEN wire from pedal interlock MUST be connected to the RED/BLUE wire.

CAD TYPE VISIO	APPLICABLE SOFTWARE		
UNIT NONE	DRAWING 1010-THROTTLE-001		
DRW SIZE A	TITLE ELECTRONIC THROTTLE- MARINE APPLICATION		
DATE 2/3/15			
SUPPLIER PART			
SCALE NONE	SHEET 5 OF 8	REVISION A	HPEVS

**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	INITIAL RELEASE	2/3/2015



2 WIRE TYPE 3  
THROTTLE


MARINE  
APPLICATION

\*\* When accelerator pedal IS PRESSED the interlock switch is released to its NORMAL position (switch not activated) thus completing the circuit since its green wire is connected to the normally closed (NC) connection.

CAD TYPE VISIO	APPLICABLE SOFTWARE		
UNIT NONE	DRAWING 1010-THROTTLE-001		
DRW SIZE A	TITLE 2 WIRE TYPE 3 THROTTLE – MARINE		
DATE 2/3/15			
SUPPLIER PART			
SCALE NONE	SHEET 6 OF 8	REVISION A	HPEVS

**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	INITIAL RELEASE	2/3/2015



3 WIRE TYPE 2  
THROTTLE


MARINE  
APPLICATION

\*\* When accelerator pedal IS PRESSED the interlock switch is released to its NORMAL position (switch not activated) thus completing the circuit since its green wire is connected to the normally closed (NC) connection.

CAD TYPE VISIO	APPLICABLE SOFTWARE		
UNIT NONE	DRAWING 1010-THROTTLE-001		
DRW SIZE A	TITLE 3 WIRE TYPE 2 THROTTLE- MARINE		
DATE 1/22/13			
SUPPLIER PART			
SCALE NONE	SHEET 7 OF 8	REVISION A	HPEVS

**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	INITIAL RELEASE	11/27/2013




## CURTIS PB8 THROTTLE ASSEMBLY

\*\* When accelerator pedal IS PRESSED the interlock switch is released to its NORMAL position (switch not activated) thus completing the circuit since its green wire is connected to the normally closed (NC) connection.

CAD TYPE VISIO	APPLICABLE SOFTWARE		
UNIT NONE	DRAWING 1010-THROTTLE-001		
DRW SIZE A	TITLE CURTIS PB8 THROTTLE		
DATE 1/22/13			
SUPPLIER PART			
SCALE NONE	SHEET 3 OF 8	REVISION A	HPEVS

**NOTICE:** This drawing is the property of Hi Performance Electric Vehicle Systems Inc., and/or its subsidiaries and affiliates (individually and collectively "HPEVS"), and contains highly proprietary, confidential, and trade secret information of HPEVS. The recipient of this drawing agrees (a) to use the information contained herein for the purpose for which it was furnished by HPEVS (b) to return this drawing upon HPEVS request. This notice shall appear on any complete or partial reproduction of this drawing.

REVISIONS		
REV	DESCRIPTION	APPROVED
A	INITIAL RELEASE	2/3/2015



3 WIRE WIG WAG  
TYPE 4  
THROTTLE\*\*

MARINE  
APPLICATION

\*\* No Forward or Reverse input used. No Interlock Switch used.

CAD TYPE VISIO	APPLICABLE SOFTWARE		
UNIT NONE	DRAWING 1010-THROTTLE-001		
DRW SIZE A	TITLE 3 WIRE TYPE 4 WIG WAG - MARINE		
DATE 2/3/15			
SUPPLIER PART			
SCALE NONE	SHEET 8 OF 8	REVISION A	HPEVS

## THROTTLE INTERLOCK CONNECTION

The throttle interlock connection is required for both 2 and 3 wire throttle pot assemblies. The Green wire is connected to the Normally Closed tab. The red/blue wire is connected to the common tab. See picture below.

NOTE: when the throttle IS ENGAGED the interlock switch is released to its NORMAL position (switch not activated) thus completing the circuit since its green wire is connected to the normally closed (NC) connection.

